GOODWOOD LED










+ Custom made design

GOODWOOD's panels are fully personalisable (colours, materials, decorative film) to match the decor of any room.

Lighting

GOODWOOD let you have an individual wall-mounted lighting unit for each bed (GOODLIGHT, LYSA, LUMIA) or an integrated cap incorporating the light sources.



TECHNICAL FEATURES


The GOODWOOD architectural concept offers many possible options for integrating electrical and medical gas equipment. Thanks to its slim profile, it is easy to incorporate into your caring area.


It can also be equipped with an optional stainless steel accessory mounting rail (25x10 mm).

1 bed standard configuration


Front view Side view

GOODWOOD with GOODLIGHT lighting unit





GOODWOOD with GOODLIGHT or LYSA lighting unit



75 mm ____ 35 mm

65 mm

LYSA

165 mm

GOODLIGHT

185 mm


65 mm


For the different colors and possible customizations, consult our architectural colour chart.

Power supply


It is designed to be fed:

From behind





From the side, via a distribution duct



Electrical equipment integration

The waterjet cutting of the GOODWOOD's cover enables exact and customized cutting. It can integrate all forms of outlets. Flush mounting of electrical equipment enables easier cleaning and disinfection of the product.



Medical gas integration

ABS / PC medical gas casings are available with a flap for AFNOR gas outlets.



Standard colours

The GOODWOOD architectural concept offers a wide range of colours. Panels have an antibacterial Sanitized® treatment.




Colors



More colors available at https://www.polyrey.com/collection/unis

Woods



More colors available at https://www.polyrey.com/collection/bois

FA Finish: Light satin finish with an extra fine grain and soft texture

EXM Finish: Extra matt with a rough texture that recreates the authenticity of the original materials

SEV Finish: The fibre of wood underpinned by a subtly irregular and silky grained surface


NB: The colors shown here may differ from finished products.


Contact our sales force to view our samples.

You can receive them within 48 hours.

TECHNICAL FEATURES

GOODWOOD with integrated aluminum profile





See the colors of laminated panels page 302

Configuration examples








2-beds Goodwood with Goodlight wall lighting unit and built-in bedside tables





TECHNICAL FEATURES



1-bed Goodwood with Goodlight wall lighting unit



1-bed Goodwood with Goodlight wall lighting unit and accessory mounting rail





Goodwood with lighting integrated RGB option



CONTROLLED LIGHTING

The GOODWOOD concept offers lighting unit on the front panel, or a GOODLIGHT unit overhanging its front panel. It also incorporates LED night light at the bottom.

High-performance and controlled lighting


The high-performance reflectors in the general and reading light units offer high efficiency and direct the light towards the middle of the room and onto the reading surface.

Comfortable lighting

The general and reading lights are less likely to dazzle the patient, medical personnel, or visitors, because the sources are not directly visible.


General lighting

- Clear satin-finish PMMA diffuser with anti-UV treatment
- MIRO 20 SILVER® Aluminum reflector




Reading lighting

- Satin-finish PMMA diffuser
- MIRO 20 SILVER® Aluminum reflector



Caring lighting


Caring lighting combines direct (reading) and indirect (general) lighting.




EFFICIENT LIGHTING

Lighting study

- Standard room
- Dimensions of the room: 3 m x 3 m, ceiling clearance 2.5 m
- Reflection coefficients: ceiling 7, walls 5, and floor 3
- Coefficient of depreciation 0.83





Lighting power (LYSA or GOODLIGHT)

Lighting	Modules power	Types of sources	Color temperature	Luminous Flux (1)	Consumption	System Efficiency	Driver(s)
General lighting	28,7 W (3 Ft)	LED	3000 K 4000 K	5039 lm	33,2 W	151,9 lm/W	Fixed / DALI
General lighting (Dynamic lighting)	38,9 W (3 Ft)	LED	2700 K to 6500 K	5000 lm	44,9 W	111,4 lm/W	DALI
Reading lighting	8,9 W (2 Ft)	LED	3000 K 4000 K	1710 lm	10,8 W	158,8 lm/W	Fixed / DALI
Night light	1 x 3,1 W	LED	3000 K	335 lm	4,9 W	68,1 lm/W	Fixed

⁽¹⁾ All the luminous flux indicated in the brochure are based on the flux of the LED modules also known as system flux.

Luminaire output flux = (Module flux) x (optical efficiency), the optical efficiency of the luminaire is indicated in the Eulumdat file (LDT line 23) available for download on our website or on request.

Dynamic Lighting



The GOODLIGHT wall lighting unit is available with dynamic lighting.

For more information, please read the dedicated brochure.









Aluminum machining Water jet machine - RX160

Woodworking

CN Biesse Rover B BT 2243




Edgebander HOMAG

Woodworking

CN Holz'her Easy Masteur 7015







Norms & certifications

- EN ISO 9001 and EN ISO 13485: Quality management systems
- \bullet CE Medical Devices Marking according to 93/42/EEC Directive
- EN ISO 11197: Medical supply units
- EN ISO 7396-1: Medical gas pipeline systems Part 1
- European rules for caring centers lighting

Bed head units, Wall lighting units, Ceiling pendants, Suspended Beams & Columns,
Special care bed head units, Sealed lightings, Medical gas monitoring & Biomedical Accessories



